

# Single locking latch - HC-B06-SL-PLBK - 1407697

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Replacement single locking latch for HEAVYCON EVO housing type B6, PA



## Key Commercial Data

Packing unit	10 STK
Minimum order quantity	10 STK
GTIN	 4 046356 777803
GTIN	4046356777803
Weight per Piece (excluding packing)	14.100 g
Custom tariff number	85389099
Country of origin	Poland

## Technical data

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

### General

Size	B6
Material	PA
Locking latch material	PA
Flammability rating according to UL 94	V0
Color	black


### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

## Drawings

# Single locking latch - HC-B06-SL-PLBK - 1407697

Dimensional drawing



Dimensional drawing

## Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27379201
eCl@ss 9.0	27440202

ETIM

ETIM 3.0	EC000796
ETIM 4.0	EC000437
ETIM 5.0	EC000437
ETIM 6.0	EC000437

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Approvals

Approvals

---

Approvals

EAC

---

Ex Approvals

---

## Single locking latch - HC-B06-SL-PLBK - 1407697

### Approvals

#### Approval details

EAC		7500651.22.01.00246
-----	---	---------------------