


## Protective cap - MSK 2 - 1665907

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

M23 metal sealing cap, for unoccupied M23 connectors, with steel wire



### Key Commercial Data

Packing unit	1 STK
GTIN	 4 017918 128098
GTIN	4017918128098
Weight per Piece (excluding packing)	15.800 g
Custom tariff number	74199990
Country of origin	Germany

### Technical data

#### Ambient conditions

Degree of protection	IP67, when in locked state
Ambient temperature (operation)	-15 °C ... 110 °C

#### General

Housing material	CuZn
Housing surface material	Nickel
Color	silver
Seal material	NBR

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Protective cap - MSK 2 - 1665907

### Classifications

#### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27261210
eCl@ss 7.0	27440208
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

#### ETIM

ETIM 3.0	EC002314
ETIM 4.0	EC002314
ETIM 5.0	EC002314
ETIM 6.0	EC002314

#### UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121421