

## TM-FF01897

### Specifications and dimensions



- Panel Mounting Fan with Filter
- Axial fan, ball bearing type
- Low Maintenance

Features	
Height	170mm
Width	157mm
Depth in front of panel	40mm
Depth behind panel	58mm
Enclosure cut out	137mm sq
Weight	1.0Kg
Operating voltage	230V AC
Free flow air volume	55m <sup>3</sup> /h
Vented air flow	42m <sup>3</sup> /h
Current consumption	100mA
Average noise level	40 dB
Ingress protection	IP55
Operating temperature	10°C to +70°C
Filtering efficiency	94%
Related Products	
Filter	TM-EF018125
Thermostat 60°C NO	TM-KTS011
Thermostat 60°C NC	TM-KTO011
Thermostat 60°C NO +NC	TM-ZR011
Hygrotherm 0-60°C 35-95%RH 230VAC	TM-ETF012
Hygrostat 35-95% RH	TM-MFR012

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com  
website: <http://www.europacomponents.com>