



TM-KTS011

Specifications and dimensions

- Thermostat
- Compact design, din rail mounting
- Bi-metal element, snap action contact

Features	
Height	60mm
Width	33mm
Depth	43mm
Weight	0.04Kg
Contact configuration	NO
Maximum switching capacity	10A 240V AC, 15A 120V AC
Maximum switching capacity	30W 24V DC
Maximum inrush current	16A AC for 10s
Ingress Protection	IP20
Maximum flexible cable size with bootlace	1.5mm ²
Tightening torque	0.5Nm
Operating Temperature	-.45°C to +80°C
Operating Humidity maximum	90% RH
Related Products	
Thermostat 60°C NC	TM-KTO011
Thermostat 60°C NO +NC	TM-ZR011
Hygrotherm 0-60°C 35-95%RH 230VAC	TM-ETF012
Hygrostat 35-95% RH	TM-MFR012

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
website: <http://www.europacomponents.com>