


TM-HG140-30W

Specifications and dimensions



- Anti-condensation Panel Heater
- Energy Saving Design
- Din Rail Mounting

Features	
Height	65mm
Width	70mm
Depth	50mm
Weight	0.3Kg
Operating voltage	110-240V AC/DC
Heating capacity	15W
Maximum inrush current	3.0A
Fuse (time delay)	2.5A
Construction	Anodised aluminium
Ingress Protection	IP20
Maximum flexible cable size with bootlace	1.5mm ²
Operating Temperature	.-45°C to +70°C
Operating Humidity maximum	90% RH
Related Products	
Thermostat 60°C NO	TM-KTS011
Thermostat 60°C NC	TM-KTO011
Thermostat 60°C NO +NC	TM-ZR011
Hygrotherm 0-60°C 35-95%RH 230VAC	TM-ETF012
Hygrostat 35-95% RH	TM-MFR012

ⓘ ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
website: <http://www.europacomponents.com>