

EDIFIER®

M2280

Slim and sleek. A 2.0 speaker set that suits your wallet and your ears.

The M2280 is a sleek 2.0 speaker set, offering great audio and an elegant design. The 3.5mm auxiliary input offers a simple plug and play option to an audio device, with volume and power buttons located on the side of the active speaker.

12W RMS of audio output is produced from two 70mm speaker drivers, with Dynamic Range Compression active. These stylish speakers offer excellent audio output, taking up minimal space ideal for desktops at home or at the office.



12
watts
R.M.S
TOTAL POWER OUTPUT



Features

- 2.0 speaker system with 12W total power output
- 3.5mm auxiliary input option
- Volume adjustment and power button located on the side of the active speaker
- 70mm speaker driver
- Universal 100V-240V power supply

Specifications

Power output	: RMS 6W x 2 (DRC On)
Signal to noise ratio	: ≥ 85dBA
Frequency response	: 95Hz - 20KHz (±12dB)
Input sensitivity	: 700mV ± 50mV
Input type	: Auxilliary
Full Range unit	: 2¾ inch (70mm), Magnetically shielded, 8Ω
EAN code	: 6923520265053 (UK)



Disclaimer: All specifications are subject to change without notice

www.edifier.com

A Passion for Sound