

# Adjustable Wire Strippers - Data Sheet

These Precision Wire Strippers feature an adjustment dial that allows the operator to select one of six different settings. A calibrated wire stop can then be adjusted for the desired insulation strip length. In a single motion, the operator squeezes and pulls the tool. This action engages four specially hardened blades to cleanly cut the wire insulation while the pulling motion breaks the insulation / conductor bond. Clean, precise strip of any insulation type. Lightweight-weighs 1 oz. Blade is hardened steel (RC58). Dimensions 3.9" x 1.6" x 0.6" (99 mm x 42 mm x 14 mm).



**ST-450**

**ST-500**

**ST-500ESD**

**ST-550**

Specifications	ST-450	ST-500	ST-500ESD	ST-550
Wire Gauge	26-36 AWG (0.40-0.12 mm)	20-30 AWG (0.80-0.25 mm)	20-30 AWG (0.80-0.25 mm)	18-28 AWG (1.00-0.30 mm)
Adj Strip-off Length	0.039-2.0" (1-50.8mm)	0.039-2.0" (1-50.8mm)	0.039-2.0" (1-50.8mm)	0.039-2.0" (1-50.8mm)
Material	ABS Housing	ABS Housing	ESD Safe Housing, Polycarbonate	ABS Housing
Dimensions	3.9" x 1.6" x 0.6" (99mm x 42mm x 14mm)	3.9" x 1.6" x 0.6" (99mm x 42mm x 14mm)	3.9" x 1.6" x 0.6" (99mm x 42mm x 14mm)	3.9" x 1.6" x 0.6" (99mm x 42mm x 14mm)
Weight	0.086 lbs (39.01 g)	0.087 lbs (39.46 g)	0.089 lbs (40.37 g)	0.088 lbs (39.92g)
UPC No	811490010192	811490010178	811490011731	811490010185