

UL SOLID UL PC 3819 18 T



Sample photo

Order symbol: UL PC 3819 18 T
Product nbr: 5320071
Description: UL Enclosure, PC
Remarks: Transparent cover

EAN: 6418074037534
El. number:
Finland:
Electric No. 8212033168
Denmark:
Electric No. Italy: 7402035U

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Rating:
Length	Width	Height		
mm:	378	188	180	
inch:	14.9	7.4	7.1	Ingress Protection (EN 60529): IP66/IP67
Materials:				Impact Resistance (EN 62262): IK08
Material:	Polycarbonate			Electrical insulation: Totally insulated
Base colour:	RAL 7035 -light grey			Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws material:	Polyamide			UV resistance: UL 508
Cover colour:	Clear transparent			Flammability Rating: UL 746C 5"
Cover screws colour:	Grey			UL Type:
Gasket material:	Polyurethane			Glow Wire Test (IEC 695-2-1) °C: 960
Temperatures:				Certificates:
Temperature °C (short term):	-40 ... 120 °C			Underwriters Laboratories
Temperature °C (continuous):	-40 ... 80 °C			SGS Fimko
Temperature °F (short term):	-40 ... 250 °F			UL Canada
Temperature °F (continuous):	-40 ... 175 °F			Gost R

SOLID 378x188x130-180

