

**UL SOLID UL PC 2819 13 G**



Sample photo

**Order symbol:** UL PC 2819 13 G  
**Product nbr:** 5320360  
**Description:** UL Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074037480  
**EI. number:**  
 Finland:  
 Electric No. 8212045185  
 Denmark:  
 Electric No. Italy: 7401020U

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Rating:
mm:	278	188	130	Ingress Protection (EN 60529): IP66/IP67
inch:	10.9	7.4	5.1	Impact Resistance (EN 62262): IK08
<b>Materials:</b>				Electrical insulation: Totally insulated
<b>Material:</b>	Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): 1
<b>Base colour:</b>	RAL 7035 -light grey			UV resistance: UL 508
<b>Cover screws material:</b>	Polyamide			Flammability Rating: UL 746C 5"
<b>Cover colour:</b>	RAL 7035 -light grey			UL Type:
<b>Cover screws colour:</b>	Grey			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Gasket material:</b>	Polyurethane			<b>Certificates:</b>
<b>Temperatures:</b>				Underwriters Laboratories
<b>Temperature °C (short term):</b>	-40 ... 120 °C			SGS Fimko
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			UL Canada
<b>Temperature °F (short term):</b>	-40 ... 250 °F			Gost R
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			

