


Stellar Labs™

Model # 24-10527



Conductor Colors

1. Blue-White/Blue
2. Orange-White/Orange
3. Green-White/Green
4. Brown-White/Brown

SPECIFICATIONS

Conductors	4 Pair
Conductor Material	bare copper Solid
Insulation Material	Polyethylene
Thickness	0.22 mm
Diameter	0.98 ± 0.01 mm
Jacket Material	PVC (CMR, CMP)
Jacket Thickness	0.55 mm (Min. Thickness: 0.50mm)
Jacket Diameter	6.2 ± 0.10 mm

ELECTRICAL PROPERTIES

Conductor Resistance	Max. 85.78 ohms/km at 20°C
Insulation Resistance	Min. 5000 mega ohms-km at 20°C
Dielectric Test	1000V DC /1 min ; No Breakdown
Temperature Rating	75°C
Voltage Rating	30V