

WB86T

Features

- Solid wood construction
- Fully enclosed
- 8" 5 oz. dual-cone speaker
- Black cloth grille
- 70/25V selectable transformer
- Push terminal speaker connection
- Lifetime warranty

Specifications

RMS Power	10W
Max. Power.....	16W
Frequency Response	85Hz – 20kHz
Rated Impedance	8 Ohms
Transformer	70/25V
Transformer Settings	10W, 5W, 2.5W, 1.25W, 0.625W & 8 Ohms
Sensitivity	93±3dB
Dimensions.....	10.41" (W) x 10" (H) x (5.43" - top / 3.19" bottom) (D)

