



Model #: CPS-1220RMS

UPC: 649532893539

MSRP: \$62.99



Title

CPS-1220RMS Rackmount PDU Power/Surge Strip - 12-Outlet 20A 2400VA 1800 Joules

Description

The CyberPower 1220RMS offers the combined functionality of both a Power Distribution Unit (PDU) and Surge Suppressor. Providing additional outlets for your rackmount power needs, this model also offers 1800 Joules of surge/lightning protection. The 1220RMS offers 12 (twelve) 20A outlets (2 front, 10 rear-mount) in the 19 inch 1U case. The rugged metal housing can withstand the most demanding environments, and a 15 ft cord ensures compatibility for most rackmount applications. Also note that CyberPower PDUs can be wall mounted, desktop, or under-cabinet mounted for use in retail, security, POS, telecommunications, networking, audio/video displays, or anywhere else dedicated power distribution is needed.

Features

- EMI/RFI Shielding: Provides shielding against electromagnetic interference & radio frequency signals. Most commonly, this is used to prevent line noise or humming that occurs over telephone lines or stereo electronics.
- LED Indicators: LED status lights indicate Power-On and wiring faults.
- Resettable Circuit Breaker: Convenient unit reset in case of an overload.
- ISO & Safety Certifications: All CyberPower manufacturing facilities are ISO-9001 Quality Tested. Our products are also UL Registered.

Technical Specifications

Technical Information	
Input Receptacles	NEMA 5-20P
Output Receptacles (Rear)	10 x NEMA 5-20R
Output Receptacles (Front)	2 x NEMA 5-20R
Power Description	
Input Voltage	110 V AC to 120 V AC
Output Voltage	120 V AC
Current	20A
Frequency	60 Hz
Load/Power Rating	2400VA
Surge Energy Rating	1800J
Filtering	EMI/RFI
Circuit Breaker	1 x 20A
Controls/Indicators	
Status Indicators	<ul style="list-style-type: none"> • Power On (Yellow) • Ground (Green) • Surge (Red)
Environmental Conditions	
Temperature	<ul style="list-style-type: none"> • 32 °F (0 °C) to 95 °F (35 °C) Operating • 5 °F (-15 °C) to 113 °F (45 °C) Non-operating
Humidity	<ul style="list-style-type: none"> • 0 to 95% Non-condensing Operating Humidity • 0 to 95% Non-condensing Non-operating
Altitude	<ul style="list-style-type: none"> • 0 ft to 10000 ft Operating • 0 ft to 50000 ft Non-operating
Physical Characteristics	
Color	Black
Form Factor	1U 19" Rack-mountable
Power Cord/Cable	1 x 15ft 20A Power Cord
Dimensions	1.75" Height x 19" Width x 4.25" Depth
Shipping Dimensions	2.25" Height x 20.5" Width x 10" Depth - Display Box
Weight	6.2 lb
Shipping Weight	6.8 lb - Display Box
Miscellaneous	
Package Contents	<ul style="list-style-type: none"> • CPS-1220RMS Unit • Warranty Card/Manual
Certifications & Standards	UL Recognized
Country of Origin	China
Warranty	
Standard Warranty	3 Year(s) Parts & Labor
Additional Warranty Information	<ul style="list-style-type: none"> • CyberPower stands behind its products by offering an industry leading 3-year warranty. CyberPower also has a #1 rated technical support team that will assist you with product, installation, or warranty concerns --- Free of charge.