

# E2270SWHN

## 54.6 cmcm (21.5 inch") LCD MONITOR

For work or home, this monitor offers excellent performance with 16.7 million colors and 5ms response time. Smart features like Eco Mode and e-Saver help you effortlessly reduce power consumption.



HDMI



TILT

### GENERAL FEATURES

Line	Value-line
Panel Type	TN
Panel Size	21.5 inch" / 54.6 cm cm
Aspect Ratio	16:9
Brightness	200 nits cd/m <sup>2</sup>
Contrast Ratio Dynamic	20M:1
Contrast Ratio Static	700:1
Pixel Pitch(H) (V)	0.248
Display Area (H x V)	476.64x268.11 mm
Viewing Angle (CR >= 10)	90/65 °
Response time	5 msms
Color	Black

### SCANNING FREQUENCY

Scanning Frequency	30-83khz/50-76hz
Pixel Frequency	108Mhz

### RESOLUTION

Maximum Resolution	1920x1080@60Hz
Recommended Resolution	1920x1080@60Hz
Colors	16.7 Million
HDCP compatible	-

### CONNECTORS

D-Sub	Yes
DVI	-
HDMI	1x
USB	-
MHL	-
DisplayPort	-

### POWER

Power Source	100 - 240V 50/60Hz
Power Consumption	On: 19W, Standby: 0.5W, Off: 0.5W
Zero Power Switch	-

### OTHER FEATURES

Vesa Wallmount	100x100
Regulations	Energystar 6 TCO no TUV-GS TUV-Bauart CE FCC EAC PVC/BRF Free ISO Certified Production RoHS compliant EUP compliant Reach compliant dicom_part_14

### ACCESSORIES

VGA Cable
HDMI Cable
Power Schuko C7 Cable

### ERGONOMIC DATA

Pivot	No
Tilt	-5/+15

### DIMENSIONS

Product with stand (W×H×D)	503,37x311,1x48 mm
Packaging (W×H×D)	560x395x110 mm
Weight	2.7 kg wo/packaging 3.45 kg w/packaging
Warranty	3 Years
EAN	4038986125321