



Main

Product or component type	Weatherproof enclosure
Enclosure type	Mini enclosure for modular device
Accessories included with enclosure	1 marking kit 2 terminal blocks 8 holes

Complementary

Enclosure mounting	Surface
Number of 18 mm modules per row	12
Total number of 18 mm modules	12
Number of horizontal rows	1
Electrical insulation class	Double insulation Class II
Provided equipment	1 marking kit 2 terminal block 8 holes
Type of front cover	Transparent
Power dissipation in W	19 W
[In] rated current	63 A
Type of rail	DIN
Number of pre-cutouts PG ISO	7
Number of terminal blocks	2 with 8 outgoers
Distribution block outgoers	8 x 10 mm ² 8 x 16 mm ²
Locking options description	Optional keylock
Enclosure material	Self-extinguishing polymer
Width	267 mm
Height	200 mm
Depth	112 mm
Colour	Door : transparent green Enclosure : light grey (RAL 7035)

Environment

Standards	EN 50102 IEC 60695-2-1 IEC 670 IEC 60439-3 EN 50262 IEC 60529
Fire resistance	650 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristic	UV resistant class 3 conforming to ISO 4582 2010 Ultraviolet degradation test conforming to ISO 4892-2 2013
Overvoltage category	II
Ambient air temperature for operation	-25...60 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------