



### Main

Product or component type	Communication card
Range compatibility	Altivar 312 Solar Altivar 312
Communication port protocol	Profibus DP
Electrical connection	1 connector RJ45, Modbus 1 removable screw terminal block for inputs/outputs Screw terminal block, Profibus DP
Transmission rate	9600 bps, 19.2, 93.75, 187.5, 500 kbps, 1.5, 3, 6 or 12 Mbps
Number of addresses	1...126

### Complementary

Input/Output number	AI2 and AI3: 2 analog input LI1...LI3: 3 logic input R2: 1 relay output
Communication service	Periodic variables output : 4 PKW and 2 PZD Periodic variables input : 4 PKW and 2 PZD Messaging via PKW periodic variables CiA 402 profile
Display type	1 LED for ST (status) 1 LED
Product weight	0.2 kg

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0939 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------