
Pomona®

Model 2224 Phenolic Box Component Mounting Banana Jack To Double Plug

Operating Temperature: +150°C. (+302°F.) Max.



MATERIALS:

Banana Plug Springs: Beryllium Copper Finish: Nickel plated Polarity Marker: Color: Red Banana Plug Bodies, Solder Turret Terminals and Banana Jacks: Brass, Alloy 360 ½ Hard. Finish: Bright tin plated Molded Housing: Electrical grade phenolic. Color: Black Marking: "MODEL 2224 POMONA

ELECTRONICS CALIF." Screws: 2 Ea., #2-56 x (3/16") P. Head – Steel Cover: Phenolic Plate. Color: Black

RATINGS:

All dimensions are in inches. Tolerances (except noted): $.xx = \pm.02$ " (,51 mm), $.xxx = \pm.005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA

6/9/99 Sales: 800-490-2361 Fax: 888-403-3360 SY/EH/LS Technical Assistance: 800-241-2060 S:\Engineering\Release\DataSheet\FlukeDataSheet\d2224_1_01.doc

ORDERING INFORMATION: Model 2224