

HMIS85

5in7 small touchscreen display front module
Backlight LED Color TFT LCD



Main

Range of product	Magelis SCU
Product or component type	Small touchscreen display HMI
Display size	5.7 inch
Pixel resolution	320 x 240 pixels QVGA


Complementary

Display type	Colour TFT LCD backlit LED
Touch panel	Analogue
Backlight lifespan	50000 hours with 65536 colours
Brightness	16 levels via touch panel
View angle horiz x vert	60° left 60° right 40° top 60° bottom
Character font	ASCII Chinese (simplified Chinese) Japanese (ANK, Kanji) Korean Taiwanese (traditional Chinese)
Width	163 mm
Depth	129.4 mm
Product weight	0.405 kg


Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1350 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Dimensions of 5.7-inches Display Module




Mounting Without an Anti-Rotation Tee



A	B (1)	B (2)
$22.50^{0/-0.30}$ mm $(0.88^{0/-0.01}$ in.)	1.5...6 mm (0.06...0.23 in.)	3...6 mm (0.11...0.23 in.)

Mounting With an Anti-Rotation Tee



C	D
$30^{0/-0.20}$ mm ($1.18^{0/-0.0007}$ in.)	$4^{0/-0.20}$ mm ($0.15^{0/-0.0007}$ in.)