



Main

Range	TeSys
Device short name	LAD4
Product or component type	Suppressor module
Product compatibility	LC1DT20...DT40 LC1D09...D38

Complementary

Mounting location	Side
Mounting mode	By clips
Suppressor technology	RC circuit
Control circuit voltage	24...48 V AC <= 400 Hz
Maximum peak voltage	3 Uc
Product weight	0.012 kg

Environment

Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...80 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------