

**Model: XTMHD**



## Xvision Analogue/AHD/IP CCTV Test Monitor

Brand	Xvision
Model Number	XTMHD
Monitor Size	3.5"
Touch Screen	Yes
Screen Resolution	480x320
Cameras Supported	Analogue/AHD/IP
AHD Camera Support	1080P/720P
IP Camera Support	Onvif
Network	RJ45 10/100, Built in Wifi
Video Input/Output	BNC
Zoom Image	Yes – Analogue/IP
Power Output	DC 12V 1Amp for Cameras
Audio Test	1 Channel Audio Signal Input, 1 Channel Audio Output
PTZ Control	RS485, Baud 600-115200bps, 30 Protocols Inc PELCO D-P
UTP Cable Tester	Cable Connection Status and Display On Screen
Network Test	IP Address Scan, Link Test, Ping Test
PoE Test	Yes
Power Input	DC 5V 1.5Amp
Battery	3.7V Lithium Polymer Battery, 3500mAh
Recharge/Operating Time	3-4 Hours Recharge / 8 Hours
Auto Off	1-30 mins
Working Temperature	-10° - +50°
Dimensions	194x112x48mm
Weight	540g
Warranty	1 Year