

FALCON NVR

4/8/CHN 5MP HD PoE NVR




HD Output



Mobile



HD IPC



CMS



DDNS



USB



Network



Mouse



PTZ



E-mail



Audio



MIC

FALCON NVR KEY FEATURES

- Up to 5MP recording
- Supports H.264 compression
- User friendly GUI
- Multi-mode recording
- Playback 4/8Chn
- 4/8port built-in PoE
- Support PTZ




FALCON NVR


4/8/CHN 5MP HD PoE NVR



Model	FALC-NVR-4 4 Channel	FALC-NVR-8 8 Channel
SYSTEM		
Compression	Standard H.264	
OS	Embedded Linux	
VIDEO		
Network Bandwidth	40 Mbps	50 Mbps
Network Input	4 Chn IPC Input	8 Chn IPC Input
Network Access	5MP/4MP/3MP/1080P/960P/720P@25/30fps	
Output	HDMIx1: 1920x1080/1280x1024	
AUDIO		
Network Input	4 Chn IPC	8 Chn IPC
Local Output	RCA x 1	
RECORD		
Record Stream	Dual stream recording	
Resolution	5MP / 4MP / 3MP / 1080P / 960P / 720P	
Mode	Manual, timer, motion, sensor	
PLAYBACK		
Simultaneous	Max 4 Chn	Max 8 Chn
Search	Time slice / time / event / tag search	
Smart Search	Highlighted colour to display the camera record in a certain period of time, different colors refers to different record events	
Function	Play, pause, FF, FB, digital zoom, etc.	
ALARM		
Mode	Manual, sensor, motion, exception	
Input	4 CH IPC	8 CH IPC
Triggering	Record, snap, preset, e-mail, etc.	
NETWORK		
Interface	RJ45 10 / 100 Mbps x 1	
PoE Port	RJ45 x 4	RJ45 x 8
Protocol	TCP / IP, PPPoE, DHCP, DNS, DDNS, UPnP, NTP, SMTP	
Web Client	Multiple users online	
STORAGE & BACKUP		
HDD	SATA x 1, max 6T	
Local Backup	U disk, USB mobile HDD	
Network Backup	Yes	
USB	USB 2.0 x 2 (one in the front panel and the other in the rear panel)	
OTHER		
Mobile Device	OS - iOS, Android	
Power Supply	DC48V	
Consumption	≤ 5W (without HDD)	
Dimensions (mm)	300 x 248 x 52 (W x D x H)	
Work Environment	-10°C~50°C, 10%-90% humidity	



Rear Panel for 4 Chn



Rear Panel for 8 Chn