



CAMBLOCK PLUS

5mm Pitch Low Profile 45° Rising Clamp Terminal Blocks

PCB
TERMINAL
BLOCKS

CTBP3000

- 2 & 3 pole interlocking
- 4-12 pole pre-assembled
- 45° mounting
- Moulded in black UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- 1.5mm² (22-14AWG)
- Captive screw
-  US &  approved



SPECIFICATION

Rating	UL=15A/300V, VDE=24A/300V
Insulation resistance	500MΩ/500V
Withstand Voltage	AC2000V/1min
Contact Resistance	20mΩ (max)
Working Temperature	-40°C to 105+°C
Mouldings	UL94-V0 Flame retardant PA66
Pin/Terminal	Tin plated brass
Rising Clamp	Brass, nickel plated
Screw/Torque	M2.5 Steel, zinc plated 0.4Nm
Recommended PCB hole size	ø1.6mm

TYPE NO.	POLES	LENGTH
CTBP3000/2	2	10mm
CTBP3000/3	3	15mm
CTBP3000/4	4	20mm
CTBP3000/5	5	25mm
CTBP3000/6	6	30mm
CTBP3000/7	7	35mm
CTBP3000/8	8	40mm
CTBP3000/9	9	45mm
CTBP3000/10	10	50mm
CTBP3000/11	11	55mm
CTBP3000/12	12	60mm

