


5mm Pitch Pluggable for Vertical or 90° Mounting Terminal Block

- 2 & 3 pole interlocking
- Moulded in black UL94-V0 PA66 flame retardant PA66
- Wire protector terminals
- Captive Screws
- 0.33-2mm² (22-14AWG)
- Guided pin alignment
- approved



TYPE NO.	POLES	LENGTH
8971297	2	10mm
8971290	3	15mm
8971294	4	20mm
8971304	5	25mm
8971307	6	30mm
8971301	7	35mm
8971310	8	40mm
8971313	9	45mm
8971317	10	50mm
8971326	11	55mm
8971329	12	60mm


SPECIFICATION	
Rating	10A 250V
Insulation resistance	5000MΩ/1000V
Withstand Voltage	AC1500V/1min
Contact Resistance	20mΩ
Working Temperature	-33°C to +120°C
Mouldings	UL94-V0 flame retardant PA66
Terminal	Tin plated brass
Wire Protector	Tin plated copper
Screw/Torque	M2.5 Steel, Nickel Plated 0.4Nm



- Supplied in 24- way strips
- Easily cut to required length
- Moulded in UL94-V0 flame retardant PA66
- 0.33-2mm² (22-14AWG)
- Anti solder wicking pins
- Guided pin alignment
- approved



SPECIFICATION	
Rating	16A 250V
Insulation resistance	5000MΩ/1000V
Withstand Voltage	AC1500V/1min
Contact Resistance	20mΩ
Working Temperature	-33°C to +120°C
Mouldings	UL94-V0 flame retardant PA66
Pin	Stainless steel
Recommended PCB hole size	ø1.6mm



TYPE NO.	POLES	DESCRIPTION
8971323	24	24 Way Pin Strip