

Masthead Amplifiers

- Professional gold plated "F" type connectors for optimal signal transfer
- Variable gain control to optimise signal strength
- Fully screened enclosure
- EPDM foam cable grip
- Low power consumption
- Tetra rejection filter on UHF input
- Requires external 12V power supply
- 5 year guarantee

	MHA26U	MHA4U
Typical Gain:	8-26dB	8-20dB
Noise:	3.5dB	3.5dB
Supply Voltage		
Current:	12V 50mA DC (both)	
Connector:	'F'	'F'

MHA26U Masthead Amplifier
MHA4U Masthead Amplifier



Masthead Power Supply Unit

- Use to power Masthead Amplifier or alternatively can be used with a Maxview (SDA6) or (DSB4/DSB8)
- Eliminates the need to add a mains socket in the loft
- Professional gold plated 'F' type connectors for optimal signal transfer
- Includes 1m power cord
- 5 year guarantee

Input Powering: 230V - 50Hz AC
Output Voltage/Current: 12V/250mA DC
Connector: 'F'

MHP1 Masthead Power Supply Unit

