

HIVIS RECHARGEABLE LED LANTERN

HV-L2R



10
HOURS
RUNTIME

250
METRE
BEAM RANGE

300
LUMENS
OUTPUT

IP44
DUST+WATER
PROOF

- » 300 Lumen white Seoul LED
- » Industrial strength copolymer housing
- » Optical Beamaster lens for beam penetration
- » Micro switch operation
- » Easy Side charging point
- » Easy screw end cap operation
- » Carry strap, battery & charger included
- » Impact resistant to 1m
- » Includes carry strap, PS-RB2Lion lithium-ion rechargeable battery and DC-USB-KIT multi-country charging kit (inc UK, EU & AUS plugs, 5v DC-USB cable and 12v USB car adaptor)

BATTERY 1 x 3.6v 2600 mAh Li-ion Rechargeable Battery (inc.)
WEIGHT 650g (with lithium-ion battery)
DIMENSION 225 x 135 x 150mm



BEAMASTER
Lenses



DC-USB-KIT CHARGING KIT (INC.)



INDUSTRIAL COPOLYMER HOUSING



SIDE CHARGING POINT



CARRY STRAP WITH CARABINERS