

Cover for Holder OG (Clip) 5x20, OG (Halter) 5x20, UH, UHB



### References

Mating cover to [OG \(Clip\) 5x20](#); [OG \(Holder\) 5x20](#); [UH](#); [UHB](#)

### Weblinks


[pdf datasheet](#), [html-datasheet](#), [General Product Information](#), [Packaging details](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

### Technical Data

Fuse-Link	5 x 20 mm
Admissible Ambient Air Temp.	-40 °C to 85 °C
Material: Cover	Thermoplastic Transparent UL 94V-0
Storage Conditions	0 °C to 60 °C, max. 70% r.h.

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [General Product Information](#)

### Dimension



### All Variants

Description	Order Number
Transparent Cover 1.6 W	<a href="#">0853.9561</a>
Transparent Cover 2.5 W	<a href="#">0853.9562</a>

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

### Packaging Unit

Plastic Bag (100 pcs.)