

# EAO – Your Expert Partner for Human Machine Interfaces

## 82-6152.01A4 - Indicator 22 mm stainless-steel

### 82-6152.01A4 - Indicator 22 mm stainless-steel



*Attention: The preview is based on a sample product. This can differ from your current configuration.*

#### Mounting

Design	flush
Mounting cut-out	Ø 22,3 mm

#### Front

Front dimension	Ø 25 mm
Front shape	round
Front ring shape	flush
Front bezel material	Stainless steel

#### Other Attributes

Operating voltage	24 V VDC
Weight	0,018 kg
Operation current	7 mA

#### Operating-/Indication part

Lens optics	opaque
Lens material	Stainless steel
Lens profile	flat
Lens illumination	illuminative
Lens colour	Stainless steel

#### IP-Rating

Front protection	IP 65, IP 67
------------------	--------------

#### Connection Method

Terminal	Screw terminal
----------	----------------

#### Illumination

Illumination	Ring with LED bi-colour red/green
--------------	-----------------------------------

#### Function

Indicator	
-----------	--

# EAO – Your Expert Partner for Human Machine Interfaces

82-6152.01A4 - Indicator 22 mm stainless-steel


## Dimensions



## Mounting cut-outs



## Wiring diagram



## Component layout

