FIBOX
Enclosing innovations

CARDMASTER PC 21/18-3

Sample photo

Order symbol:	PC 21/18-3	**EAN**:	6418074056733
Product nbr:	7525154	**El. number**:	
Description:	Enclosure, PC	Finland:	3438231
Remarks:	Smoked transparent hinged cover	Electric No. Denmark:	8212016664
		Electric No. Sweden:	2537306

Including: Base, terminal compartment cover with PUR gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:	**Length**	**Width**	**Height**
mm:	235	185	119
inch:	9.3	7.3	4.7

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	Smoked grey
Gasket material:	EPDM & PUR

Temperatures:

Temperature °C (short term):	-40 … 120 °C
Temperature °C (continuous):	-40 … 80 °C
Temperature °F (short term):	-40 … 250 °F
Temperature °F (continuous):	-40 … 175 °F

Accessories:

MP 21/18	Mounting plate

Accessories:

FP 21/18	Front plate (aluminium)
FC PC 21/18	Frame of PC front plate

Rating:

Ingress Protection (EN 60529): IP65
Impact Resistance (EN 62262): IK07/IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 3, 3R, 4X, 12, 13

Certificates:

SGS Fimko
Gost R



© Fibox Oy, Data subject to change without notice (printed: 26.7.2017)