

CAB CAB ABS 504020 G



Sample photo

Order symbol: CAB ABS 504020 G
Product nbr: 8183360
Description: Cabinet, ABS, Grey door
Remarks: Latches on the long side

EAN: 6418074020383
EI. number:
 Finland: 3424320
 Electric No. Denmark: 8212020566
 Electric No. Italy: 7811055
 Electric No. Sweden: 2540077

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:			Accessories:	
Length	Width	Height		
mm:	500	400	EKIV 37	DIN-35 Mounting rail
inch:	19.7	15.7	DS35370E1	DIN-35 Mounting rail
			EKIV 47	DIN-35 Mounting rail
			DS35470E1	DIN-35 Mounting rail
Materials:			FP A 54	Swing-out door/Front plate
Material:	ABS		MB 12225 AL	Swing door set
Base colour:	RAL 7035 -light grey		FP 54	Front plate
Cover colour:	RAL 7035 -light grey		FP 18X2-54	Front plate
Gasket material:	Polyurethane		DRF 54	DIN rail frame set
Temperatures:			Rating:	
Temperature °C (short term):	-40 ... 80 °C		Ingress Protection (EN 60529): IP65	
Temperature °C (continuous):	-40 ... 60 °C		Impact Resistance (EN 62262): IK08	
Temperature °F (short term):	-40 ... 175 °F		Electrical insulation: Totally insulated	
Temperature °F (continuous):	-40 ... 140 °F		Halogen free (DIN/VDE 0472, Part 815): 1	
			Flammability Rating: UL 94 HB	
			Glow Wire Test (IEC 695-2-1) °C: 650	
			NEMA Class: NEMA 1, 4, 4X, 12, 13	
Accessories:			Certificates:	
EKIV 54	Mounting plate		SGS Fimko	
			Gost R	

