

**CAB CAB ABS 303018 T**



Sample photo

**Order symbol:** CAB ABS 303018 T  
**Product nbr:** 8183040  
**Description:** Cabinet, ABS  
**Remarks:** Latches on the long side

**EAN:** 6418074020178  
**EI. number:**  
 Finland: 3424357  
 Electric No. 8212020537  
 Denmark:  
 Electric No. Italy: 7812025  
 Electric No. Sweden: 2540037

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	300	300	180	EKIV 27	DIN-35 Mounting rail
inch:	11.8	11.8	7.1	DS35270E1	DIN-35 Mounting rail
<b>Materials:</b>				FP A 33	Swing-out door/Front plate
<b>Material:</b>	ABS			MB 12225 AL	Swing door set
<b>Base colour:</b>	RAL 7035 -light grey			FP 33	Front plate
<b>Cover colour:</b>	Smoked grey			FP 12-33	Front plate
<b>Gasket material:</b>	Polyurethane			FP 12x2-33	Front plate
<b>Temperatures:</b>				DRF 33	DIN rail frame set
<b>Temperature °C (short term):</b>	-40 ... 80 °C			<b>Rating:</b>	
<b>Temperature °C (continuous):</b>	-40 ... 60 °C			Ingress Protection (EN 60529): IP65	
<b>Temperature °F (short term):</b>	-40 ... 175 °F			Impact Resistance (EN 62262): IK08	
<b>Temperature °F (continuous):</b>	-40 ... 140 °F			Electrical insulation: Totally insulated	
<b>Accessories:</b>				Halogen free (DIN/VDE 0472, Part 815): 1	
EKIV 33	Mounting plate			Flammability Rating: UL 94 HB	
				Glow Wire Test (IEC 695-2-1) °C: 650	
				NEMA Class: NEMA 1, 4, 4X, 12, 13	
				<b>Certificates:</b>	
				SGS Fimko	
				Gost R	

