

**CAB CAB PC 303018 T3B**



Sample photo

**Order symbol:** CAB PC 303018 T3B  
**Product nbr:** 8113042  
**Description:** Cabinet, PC  
**Remarks:** Lock on the long side

**EAN:** 6418074020154  
**EI. number:**  
 Finland: 3424161  
 Electric No. Denmark: 8212019234  
 Electric No. Italy: 7822030  
 Electric No. Sweden: 2539943

Including: Cabinet base, door with PUR gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:	Length	Width	Height	Accessories:	
mm:	300	300	180	EKIV 27	DIN-35 Mounting rail
inch:	11.8	11.8	7.1	DS35270E1	DIN-35 Mounting rail
				FP A 33	Swing-out door/Front plate

Materials:		Accessories:	
<b>Material:</b>	Polycarbonate	MB 12225 AL	Swing door set
<b>Base colour:</b>	RAL 7035 -light grey	FP 33	Front plate
<b>Cover colour:</b>	Smoked grey	FP 12-33	Front plate
<b>Gasket material:</b>	Polyurethane	FP 12x2-33	Front plate
		DRF 33	DIN rail frame set

Temperatures:		Rating:	
<b>Temperature °C (short term):</b>	-40 ... 120 °C	Ingress Protection (EN 60529): IP65	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C	Impact Resistance (EN 62262): IK08	
<b>Temperature °F (short term):</b>	-40 ... 250 °F	Electrical insulation: Totally insulated	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F	Halogen free (DIN/VDE 0472, Part 815): 1	
		UV resistance: UL 508	
		Flammability Rating: UL 746C 5"	
		Glow Wire Test (IEC 695-2-1) °C: 960	

Accessories:		Certificates:	
EKIV 33	Mounting plate	Germanischer Lloyd (GL)	
		SGS Fimko	
		Lloyds Register of Shipping (LR)	
		Gost R	

