

CARDMASTER ABS 30/25-3



Order symbol: ABS 30/25-3
Product nbr: 7585019
Description: Enclosure, ABS
Remarks: Smoked transparent hinged cover

EAN: 6418074056795
EI. number:
 Finland: 3438245
 Electric No. Denmark: 8212016774
 Electric No. Sweden: 7585019

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:		Length	Width	Height	Accessories:	
mm:		320	260	129	FP 30/25	Front plate (aluminium)
inch:		12.6	10.2	5.1	FC PC 30/25	Frame of PC front plate
Materials:		Rating:				
Material:	ABS	Ingress Protection (EN 60529): IP65				
Base colour:	RAL 7035 -light grey	Impact Resistance (EN 62262): IK07				
Cover colour:	Smoked grey	Electrical insulation: Totally insulated				
Gasket material:	EPDM & PUR	Halogen free (DIN/VDE 0472, Part 815): 1				
Temperatures:		Flammability Rating: UL 94 HB				
Temperature °C (short term):	-40 ... 80 °C	Glow Wire Test (IEC 695-2-1) °C: 650				
Temperature °C (continuous):	-40 ... 60 °C	NEMA Class: NEMA 1, 3, 3R, 12, 13				
Temperature °F (short term):	-40 ... 175 °F	Certificates:				
Temperature °F (continuous):	-40 ... 140 °F	Gost R				
Accessories:		MP 30/25				
	Mounting plate					

