

**TEMPO TA191209**



**Order symbol:** TA191209  
**Product nbr:** 5814000  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074060723  
**EI. number:**  
**Finland:** 3435682  
**Electric No. Denmark:** 8212035001  
**Electric No. Sweden:** 5814000

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

Dimensions:				Accessories:	
Length	Width	Height			
mm:	187	122	90	MIV 10	DIN-35 Mounting rail
inch:	7.4	4.8	3.5	DH-3	DIN-35 Mounting rail
<b>Materials:</b>				FP 10674	
<b>Material:</b>	ABS			DPS 14553	Grey sealing plug set
<b>Base colour:</b>	RAL 7035 -light grey			<b>Rating:</b>	
<b>Cover screws material:</b>	Polyamide			Ingress Protection (EN 60529): IP65	
<b>Cover colour:</b>	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07	
<b>Cover screws colour:</b>	Grey			Electrical insulation: Totally insulated	
<b>Gasket material:</b>	Polyurethane			Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Temperatures:</b>				Flammability Rating: UL 94 HB	
<b>Temperature °C (short term):</b>	-40 ... 80 °C			Glow Wire Test (IEC 695-2-1) °C: 650	
<b>Temperature °C (continuous):</b>	-40 ... 60 °C			<b>Certificates:</b>	
<b>Temperature °F (short term):</b>	-40 ... 175 °F			SGS Fimko	
<b>Temperature °F (continuous):</b>	-40 ... 140 °F				
<b>Accessories:</b>					
MP 1912	Mounting plate				

