

**MNX PC 150/75 HT**



Sample photo

**Order symbol:** PC 150/75 HT  
**Product nbr:** 6011914  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent cover

**EAN:** 6418074022424  
**El. number:**  
 Finland: 3420463  
 Electric No. 8212022470  
 Denmark:  
 Electric No. Italy: 7352095  
 Electric No. Sweden: 2535654

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
<b>mm:</b>	180	130	75	MIN 10	DIN-15 Mounting rail
<b>inch:</b>	7.1	5.1	3.0	MIN 15	DIN-15 Mounting rail
<b>Materials:</b>				MIV 10	DIN-35 Mounting rail
<b>Material:</b>	Polycarbonate			MIV 15	DIN-35 Mounting rail
<b>Base colour:</b>	RAL 7035 -light grey			FP A 150/180	Front plate (Aluminium)
<b>Cover screws material:</b>	Polyamide			HFP 180	Front plate hinge series
<b>Cover colour:</b>	Smoked grey			FP 22046	Wall fastening lug (4 pcs)
<b>Cover screws colour:</b>	Black			<b>Rating:</b>	
<b>Gasket material:</b>	TPE			Ingress Protection (EN 60529): IP66/IP67	
<b>Temperatures:</b>				Impact Resistance (EN 62262): IK08	
<b>Temperature °C (short term):</b>	-40 ... 120 °C			Electrical insulation: Totally insulated	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Temperature °F (short term):</b>	-40 ... 250 °F			UV resistance: UL 508	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			Flammability Rating: UL 746C 5"	
<b>Accessories:</b>				Glow Wire Test (IEC 695-2-1) °C: 960	
MIV 150	Mounting plate (Galvanized steel)			NEMA Class: NEMA 1, 4, 4X, 6	
				<b>Certificates:</b>	
				Germanischer Lloyd (GL)	
				SGS Fimko	
				Gost R	

