


MNX PC 175/75 HT



Sample photo

Order symbol: PC 175/75 HT
Product nbr: 6011920
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074024435
EI. number:
 Finland: 3422254
 Electric No. Denmark: 8212022690
 Electric No. Italy: 7352113
 Electric No. Sweden: 2535664

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions: Length Width Height **Accessories:**

mm:	180	180	75
inch:	7.1	7.1	3.0

MIN 15	DIN-15 Mounting rail
MIV 15	DIN-35 Mounting rail
FP A 175/180	Front plate (Aluminium)
HFP 180	Front plate hinge series
FP 22046	Wall fastening lug (4 pcs)

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	Smoked grey
Cover screws colour:	Black
Gasket material:	TPE

Rating:

Ingress Protection (EN 60529): IP66/IP67
 Impact Resistance (EN 62262): IK08
 Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): 1
 UV resistance: UL 508
 Flammability Rating: UL 746C 5"
 Glow Wire Test (IEC 695-2-1) °C: 960
 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Certificates:

Germanischer Lloyd (GL)
 SGS Fimko
 Gost R

Accessories:

MIV 175	Mounting plate (Galvanized steel)
---------	-----------------------------------

