

SOLID PC 3828 13 T-2FSH



Sample photo

Order symbol: PC 3828 13 T-2FSH
Product nbr: 2539551
Description: Enclosure, PC
Remarks: Transparent hinged cover

EAN: 6418074052865
EI. number:
 Finland: 3435754
 Electric No. Sweden: 2539551

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:			Accessories:	
Length	Width	Height		
mm:	378	278	EKPXT	Mounting plate isolated
inch:	14.9	10.9	EKV 22	DIN-35 Mounting rail
			EKV 32	DIN-35 Mounting rail
			EKPZR	Extension frame
Materials:			Rating:	
Material:	Polycarbonate		Ingress Protection (EN 60529): IP65	
Base colour:	RAL 7035 -light grey		Impact Resistance (EN 62262): IK08/IK09	
Cover screws material:	Polyamide		Electrical insulation: Totally insulated	
Cover colour:	Clear transparent		Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey		UV resistance: UL 508	
Gasket material:	Polyurethane		Flammability Rating: UL 746C 5"	
			Glow Wire Test (IEC 695-2-1) °C: 960	
Temperatures:			Certificates:	
Temperature °C (short term):	-40 ... 120 °C		SGS Fimko	
Temperature °C (continuous):	-40 ... 80 °C		Gost R	
Temperature °F (short term):	-40 ... 250 °F			
Temperature °F (continuous):	-40 ... 175 °F			
Accessories:				
EKPVT	Mounting plate			

