

POE power output	No support	48V PoE power output, Max up 24W	48V PoE power output, Max up 24W	48V PoE power output, Max up 24W	48V PoE power output, Max up 24W	48V PoE power output, Max up 24W	48V PoE power output, Max up 24W	48V PoE power output, Max up 24W
12V power output	12V 2A power output	12V 2A power output	12V 2A power output	12V 2A power output	12V 2A power output	12V 2A power output	12V 2A power output	12V 2A power output
USB 5V power output	Support, as power bank for mobile phones	Support, as power bank for mobile phones	Support, as power bank for mobile phones	Support, as power bank for mobile phones	Support, as power bank for mobile phones	Support, as power bank for mobile phones	Support, as power bank for mobile phones	Support, as power bank for mobile phones
Optionals functions (* means the function is optional)								
Cable tracer *	Come with cable tracer, find a connected cable from a bundle of cables using audio tones	No support	No support	Come with cable tracer, find a connected cable from a bundle of cables using audio tones	Come with cable tracer, find a connected cable from a bundle of cables using audio tones	No support	No support	No support
Video level meter *	Come with analog video level meter, perform NTSC and PAL video amplitude signal measurements for PEAK to PEAK, SYNC level and COLOR BURST chroma level	No support	No support	Come with analog video level meter, perform NTSC and PAL video amplitude signal measurements for PEAK to PEAK, SYNC level and COLOR BURST chroma level	Come with analog video level meter, perform NTSC and PAL video amplitude signal measurements for PEAK to PEAK, SYNC level and COLOR BURST chroma level	No support	No support	No support
HD-TVI test *	No support	No support	TVI 3.0, support 5MP TVI test, 2560x1944P 12.5FPS	No support	TVI 3.0, support 5MP TVI test, 2560x1944P 12.5FPS	No support	TVI 3.0, support 5MP TVI test, 2560x1944P 12.5FPS	5MP TVI test, 2560x1944P 12.5FPS
HD-CVI test *	No support	No support	support 2MP CVI	No support	support 2MP CVI	No support	support 2MP CVI	4MP CVI test, 2560x1440P 25F/30F
AHD test *	No support	No support	support 2MP AHD	No support	support 2MP AHD	No support	support 2MP AHD	3MP/4MP AHD test, 2560x1440P 15F/25F/30F

SDI Input	1 channel HD-SDI input, supports 1080P	No support	No support	No support	No support	No support	1 channel HD-SDI input	1 channel HD SDI/EX SDI input
SDI Output	1 channel HD-SDI output, supports 1080P	No support	No support	No support	No support	No support	No support	No support
VGA input	1 channel VGA input	No support	No support	No support	No support	No support	No support	No support
Power adapter	DC 5V (2A)	DC 12V (2A)	DC 12V (2A)	DC 12V (2A)	DC 12V (2A)	DC 12V (2A)	DC 12V (2A)	DC 12V (2A)
Working time	16 hours	16 hours	16 hours	16 hours	16 hours	10 hours	10 hours	10 hours