

USB 2.0 Booster Extension Cable

GUE2118



- Built-in booster chipsets - Amplifies high-speed USB signals
- Daisy chainable - Three units to support up to 117 ft.
- USB 2.0 transfer rates up to 480Mbps
- Compact size with patent pending secured lock mechanism
- Plug-and-Play, no drivers or power supply needed
- Centralize USB devices and keep desktop workspace clean
- 39 ft. long
- PC or Mac compatible


The IOGEAR USB 2.0 Booster Extension Cable uses active electronics to amplify the USB signal beyond the USB 2.0 specification of 15 feet. It does this with no loss of data integrity or signal quality. The cable has male and female USB type "A" connectors. The USB "A" connector is the rectangular shaped plug found on PC's, hubs, and many other host interfaces. The IOGEAR USB 2.0 Booster Extension Cable extends from the host and provides another female "A" connector for longer distance USB needs.

The cable is transparent to the host and the device and it is compatible with any O/S or USB accessory. It is ideal for applications that require distance, for example placing a printer in the office or home where more users have easier access. The IOGEAR USB 2.0 Booster Extension Cable is Plug-and-Play, no additional drivers or complicated set up required. The solution can also give you the ability to daisy-chain a maximum of three cables together in order to reach up to a total of 117 feet of USB High-Speed connection.

USB 2.0 Booster Extension Cable

How does it work?

- USB 2.0 Devices such as web cam, printer and hard drive
- PC or Mac



Note: USB cable used to connect USB device and GUE2118 is sold separately

Requirements:

- Available USB port on PC / Mac
- Windows 98SE, Windows ME, Windows 2000, Windows XP, Windows Vista, Windows 7 (32- & 64-bit OS)
- Mac OS 8.6 and above
- Linux Kernel 2.4.20 and above

Package Contents:

- 1 x GUE2118
- 1 x Quick Start Guide
- 1 x USB Type 'A' Female Adapter
- 1 x Warranty Card

SPECIFICATIONS

Function	
Cable Length	39 feet
Computer Interface	USB Type A
Daisy Chain	Up to 3 level daisy chain
Device Connection	USB Type A
Environment	
Operation Temperature	32 to 158 degree Fahrenheit
Storage Temperature	-67 to 302 degree Fahrenheit
USB Specification	Compatible with USB 2.0/1.1
Transfer Rate	Up to 480Mbps

Dimensions	
POP Information	
10" Peg Hook	4
6" Peg Hook	2
Unit Dimensions	
Length	39 ft.
Inner Pack	
Width	7.5"
Height	9"
Depth	7"
Inner Pack Qty.	3
Unit Package Dimensions	
Width	6"
Height	8"
Depth	2.5"
Master Carton	
Width	8.5"
Height	10"
Depth	15"
Master Carton Qty.	6
Weight	
Master Carton Wt.	9.05 lb
Inner Pack Wt.	4.1 lb
Unit Pack Wt.	1.2 lb
Unit Wt.	1.05 lb