

KFM LED

# KFL026128

Old item no.: 18255LG



## KFM LED-2/FE 5D LIGHT GREY

KFM LED produces nearly 75% greater light output than traditional KFM models. A heavy-duty, all-metal construction with sleek design, adjustable arm and excellent light output makes the KFM suitable for a variety of industrial applications. No knobs to tighten, nothing to adjust. A flexible, self-balancing shade and fully-enclosed, hands-free neck design combined with 30" heavy-duty internal-spring parallel, three-pivot K-arm, allows the lamp head to be secured in any position and are ideal for environments where FOD is a concern. The quality and positioning of the LEDs across two semi-circular modules allows for virtually shadow-free 5-diopter (2.25X) magnification and excellent color rendition. Weighted base. Color: light grey.



### Lightsource

Number of lamps	1
Lamp power (W)	11
Lightsource	LED
CRI and/or Color Temperature	80 CRI, 4000K
Lumen/Watt	82
Lumen Out	900

### Optic

Primary Lens (D)	5
Working distance (mm)	200
Magnification (X)	2.25

### Technical data

Maximum ambient temperature (°C)	25
IP classification	20

### Electrical data

Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Maximum voltage (V)	120
Voltage from (V)	100
Total consumption (W)	11

### Dimensions

Net weight (kg)	0
Arm length (in.)	30

### Body

Body color	Grey
------------	------

### Termination

Mounting	Table/desk base
----------	-----------------