

00 21 30

Tool Case "Electric" 23 parts



- Contains 23 brand name quality tools, partly VDE tested according to DIN EN/IEC 60900
- Hard-wearing ABS hard-shell construction with aluminium frame and circular buffer protection
- Document compartment and pen holding straps
- One removable tool plate, with elastic loops on both sides
- One cover plate with elastic loops and tool protection cloth
- Large base tray with variable separations (e.g. for measuring and testing devices). Interior dimensions: 420 x 320 x 85 mm
- Sturdy metal locks and 3-digit-lock
- Strong, ergonomic handle
- Feet on both sides
- Colour: silver / aluminium look






































Article No.	00 21 30
EAN	4003773051084
Net weight g	9440

technical change and errors excepted



Content 00 21 30 (23)

Article No.		Quantity	
00 11 01	KNIPEX TwinKey®, for all standard cabinets and shut-off systems	1	
03 06 180	Combination Pliers	1	⚠ 1000 V ⚡ ⚙️ 🔧 🔪
12 40 200	Self-Adjusting Insulation Stripper	1	⚡
16 95 01 SB	KNIPEX ErgoStrip®, Universal Dismantling Tool	1	⚡
26 16 200	Snipe Nose Side Cutting Pliers, (Stork Beak Pliers)	1	⚠ 1000 V ⚡ ⚙️ ⚙️ 🔧 🔪
26 26 200	Snipe Nose Side Cutting Pliers, (Stork Beak Pliers)	1	⚠ 1000 V ⚡ ⚙️ ⚙️ 🔧 🔪 40°
70 06 125	Diagonal Cutter	1	⚠ 1000 V ⚡ ⚙️ 🔧 🔪
70 06 160	Diagonal Cutter	1	⚠ 1000 V ⚡ ⚙️ 🔧 🔪
86 03 180	Pliers Wrench, pliers and a wrench in a single tool	1	🔧 🔪
87 03 250	KNIPEX Cobra®, Hightech Water Pump Pliers	1	🔧 🔪
92 27 62	Precision Tweezers, insulated	1	⚠ 1000 V ⚡ 🔧 🔪
98 20 25	Screwdrivers for slotted screws	1	⚠ 1000 V ⚡ ⚙️ 🔧
98 20 35 SL	Screwdriver (Slim) for slotted screws	1	⚠ 1000 V ⚡ ⚙️ 🔧

98 20 40 SL	Screwdriver (Slim) for slotted screws	1	 1000 V   
98 20 55 SL	Screwdriver (Slim) for slotted screws	1	 1000 V   
98 20 65 SL	Screwdriver (Slim) for slotted screws	1	 1000 V   
98 20 80	Screwdrivers for slotted screws	1	 1000 V   
98 24 00	Screwdriver for cross recessed screws, Phillips®	1	 1000 V   
98 24 01 SL	Screwdriver (Slim) for cross-recessed screws, Phillips®	1	 1000 V   
98 24 02 SL	Screwdriver (Slim) for cross-recessed screws, Phillips®	1	 1000 V   
98 25 01 SL	Screwdriver (Slim) for cross-recessed screws, Pozidriv®	1	 1000 V   
98 25 02 SL	Screwdriver (Slim) for cross-recessed screws, Pozidriv®	1	 1000 V   
98 56	Cable Knife, with replaceable blade	1	 1000 V 