

JAC-PLUS-RJ11

Entry level headset with a direct plug-in RJ11 jack

NEW



RJ11 JACK



CLOTHING CLIP

KEY FEATURES

- Single and Dual ear option available.
- Single earpiece allowing users to confer with colleagues.
- Left / right ear side compatible.
- Supplied with standard RJ11 jack.
- Fully flexible microphone for exact positioning.
- Noise cancelling microphone.
- Acoustic shock protection.
- Sure fit fully adjustable headband.
- Clothing clip included.
- Lightweight headset, ~ 36g / ~68g
- 12 month repair or replacement warranty.

TECHNICAL DATA

Microphone:	
Pattern:	Electret
Impedance:	Max. 3.9KΩ
Sensitivity:	-43±3dB at 1kHz
Frequency Range:	100-10000Hz
Operating Temp:	-20°C ~ +60°C
Storage Temp:	-40°C ~ +70°C
Speaker:	
Pattern:	Dynamic moving coil
Impedance:	150Ω / 300Ω
Sound Pressure:	94±3dB / 91±3dB at 1kHz
Sound Intensity:	80mW / 40mW
Frequency range:	300~3.4 kHz
Operating Temp:	-20°C ~ +60°C
Storage Temp:	-40°C ~ +70°C

HOME	✓
SMALL OFFICE	✓
OFFICE	✓
CALL CENTRE	✗
MOBILE	✓
LIGHT USER	✓
MEDIUM USER	✓
HEAVY USER	✗
EXTREME USER	✗