

MA30

Half rack mixing amplifier, 30W @
100 volt



During the redefining process of the mixing amplifier one of the key-conclusions was to bring it back to basics and make it user-friendly. The cutting-edge Apart MA30 has an unseen intuitive user interface and ground breaking, logic and sheer rear panel. The volume control rotary on the front panel is prominent, illuminated, bigger and put in the forefront while the mic volume control is smaller and recessed. The MA30 comes in a compact 9.

5" housing with 1 mic/line input and 2 stereo line, mono summed inputs. The smart left-to-right 4 level priority and rear panel design makes it intuitive for installers. On the rear panel you can find an emergency input, paging mic with chime and a 24VDC override output. Every end-user and installer will instantly see and understand how to operate or install this progressive MA30 mixing amplifier.

TECHNICAL SPECIFICATIONS

height- rack units (1U=44 mm) in U	2	depth (build in) in mm	240
depth (incl front) in mm	250	power supply	100 - 240 VAC
power consumption (max) in watts	60	output power RMS 100 volts in watts	30
output power RMS 4 ohms in watts	30	dynamic output power 100 volts in watts	30
minimum impedance load in ohms	4	output power tapings	70 - 100 volts - 4 ohms
zone outputs	1	MIC inputs balanced	2
inputs with Phantom power	1	line input unbalanced	2
tone control	yes	priority switch	2
VOX mute	yes	chime	yes
emergency input	1	priority output	1
priority levels	4	power amp topology	class-D
frequency response (in Hz)	60 - 20 k	cooling system	convection
applicable in 100V	yes	applicable low impedance	yes
Net weight product (kg)	2.4		

MORE PICTURES

