




Datenblatt - Fiche technique - Data sheet

21.15.0833



ROLINE S/FTP-(PiMF-)Patchkabel Kat.6, 3m, grau


Cordon ROLINE Cat.6 S/FTP (PiMF) gris, 3,0m

ROLINE S/FTP (PiMF) Patch Cord, Cat.6, grey, 3 m


Total length (optional)



A



B



C

Remark : SCAEAXX017X XXX X E1201

(1) (2) (3) (4)

(1) XX : Jacket Color

- 01=Black(RAL9011), 02=Gray(RAL7035), 03=Red(RAL3031)
- 05=White(RAL9010), 06=Yellow(RAL1021), 07=Blue(RAL5015)
- 08=Green(RAL6029), 09=Orange(RAL2003), 10=Purple(RAL4005)
- 11=Pink(RAL4003)

(2) X : Wiring

1=T568A, 2=T568B, 3=T568A & T568B combination

(3) XXX : Length

(4) Length Unit : 1=cm, 2=meter, 3=feet.

- (3)(4) : 0301=0.3meter(30cm) 0501=0.5meter(50cm),
- 0012=1meter, 0102=10meter
- 0033=3feet, 0103=10feet

Remark#

21.15.0823	1.5m	grey	21.15.1346	2.0m	white
21.15.0824	1.5m	red	21.15.1356	3.0m	white
21.15.0825	1.5m	yellow	21.15.1366	5.0m	white
21.15.0826	1.5m	green	21.15.1376	7.0m	white
21.15.0827	1.5m	blue	21.15.1386	10m	white
21.15.0828	1.5m	black	21.15.1396	15m	white
21.15.0829	1.5m	white	21.15.1406	20m	white
21.15.1316	0.3m	white			
21.15.1326	0.5m	white			
21.15.1336	1.0m	white			

Specification :

Material :

1. RJ45 Plug : (JE P/N : P028850)
- 1-1. Housing : Polycarbonate, UL 94V-2, Transparent color.
- 1-2. Contact material : Phosphor Bronze with 50-60 micro-inch Nickel plated.
- 1-3. Contact finished : Min. 50 micro-inch Gold plated on surface contact area.
- 1-4. Shield : Bronze with Nickel plated.
2. Molding : PVC.
3. Cable :
 - 3-1. Jacket : PVC.
 - 3-2. Conductor : 26 AWG stranded copper.
 - 3-3. Isolation : PE.
 - 3-4. Shield : Aluminum Foil Shielded for Each Pair, Tin Copper Braid.
4. Cable structure : S/FTP, 4 twisted pair.

Rotronic Co.,Ltd.

GENERAL TOLERANCE OF DIMENSIONS	DRAWING	10.JAN.2011	Abby
X.XXX ±0.005	CHECK	10.JAN.2011	Maer
X.XX ±0.05	APPROVAL	10.JAN.2011	YTY
X.X ±0.1	SCALE	1/1 (A4)	UNIT mm
		DATE	NAME
			ITEM NO.:SCAEAXX017XXXXXE1201
			DES.: C6 S/FTP Patch Cord
			DRAWING NO. SCAEAXX017XXXXXE1201(SA1)
			DRAWING CLASSIFICATION S SHEET 1 OF 1

