

Microscope Lighting/Digital Options

18746

Old item no.: 18746



LED RING LIGHT, DIMMING

Dimmable LED Ring Light maximizes light output and distribution while preventing harmful glare and reflections. Its modular construction, paired with brilliant 40 LED display and 6000-K color temperature, makes this ring light ideal for the inspection of surface cracks and defects as well as lead-free inspection. 9-watts of pure-white LED light produce up to 3600 footcandles at 4.5" working distance and ease the examination of welds, solder joints, flux residues and hairline stress cracks. A removable/replaceable diffuser allows for easy cleaning. Dimmable to 15% output. A 50,000 hour lumen maintenance (lamp life) makes this LED ring light suitable as a replacement for traditional 150W Fiber Optic Illuminators.



Dimensions

Net weight (kg)

0