



Quality Products. Service Excellence.

## Formed Steel Rack Panels *PBFS Series*

Also referred to as a Spacer Blank Panel

### Features

- Constructed of 16-gauge steel.
- Fits standard EIA-310-D compliant rails.
- Install in unused rack space to improve both cooling efficiency and prevent air re-circulation.
- Finished in smooth powder paint.
- RoHS Compliant.
- Manufactured in North America.



### Accessories

- Mounting Hardware



Part No. Gloss Black	Part No. Matte Black	Part No. ASA 61 Gray	Part No. RAL 7035 Light Gray	Panel Height		Number of Mounting Slots
				Units	Rack Units	
PBFS19000BK2	PBFS19000BK	-	-	0.088	1/2U	2
PBFS19001BK2	PBFS19001BK	PBFS19001GY2	PBFS19001LG2	1.75	1U	4
PBFS19003BK2	PBFS19003BK	PBFS19003GY2	PBFS19003LG2	3.50	2U	4
PBFS19005BK2	PBFS19005BK	PBFS19005GY2	PBFS19005LG2	5.25	3U	4
PBFS19007BK2	PBFS19007BK	PBFS19007GY2	PBFS19007LG2	7.00	4U	4
PBFS19008BK2	-	PBFS19008GY2	PBFS19008LG2	8.75	5U	4
PBFS19010BK2	-	PBFS19010GY2	PBFS19010LG2	10.50	6U	8
PBFS19012BK2	-	PBFS19012GY2	PBFS19012LG2	12.25	7U	8
PBFS19014BK2	-	PBFS19014GY2	PBFS19014LG2	14.00	8U	8
PBFS19015BK2	-	PBFS19015GY2	PBFS19015LG2	15.75	9U	8
PBFS19017BK2	-	PBFS19017GY2	PBFS19017LG2	17.50	10U	8
PBFS19019BK2	-	PBFS19019GY2	PBFS19019LG2	19.25	11U	8
PBFS19021BK2	-	PBFS19021GY2	-	21.00	12U	8
PBFS19022BK2	-	PBFS19022GY2	PBFS19022LG2	22.75	13U	8
PBFS19024BK2	-	PBFS19024GY2	-	24.50	14U	10
PBFS19026BK2	-	PBFS19026GY2	-	26.25	15U	10
PBFS19028BK2	-	PBFS19028GY2	-	28.00	16U	12
PBFS19029BK2	-	PBFS19029GY2	-	29.75	17U	12
PBFS19031BK2	-	PBFS19031GY2	-	31.50	18U	12

Tags: Flanged, Folded

Data subject to change without notice

© 2017. Hammond Manufacturing Ltd. All rights reserved.

