

Side panel - UCS SW 87-F 9005 - 2203359


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Side panel for use with housing half shells 125 x 87 mm in size; panel thickness: 2 mm; total height of housing: 47 mm; material: polycarbonate; color: black similar to RAL 9005



Key Commercial Data

Packing unit	20 STK
GTIN	 4 055626 427751
GTIN	4055626427751
Weight per Piece (excluding packing)	5.400 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

General

Housing material	PC
------------------	----

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 100 °C (depending on power dissipation)

Dimensions

Width	58 mm
Height	39.5 mm
Depth	2 mm

Classifications

eCl@ss

eCl@ss 5.1	27180506
------------	----------

Side panel - UCS SW 87-F 9005 - 2203359

Classifications

eCl@ss

eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031