

SLIMLINE LAMP WITH ON/OFF SWITCH

SL 025



- > Slim casing
- > Electronic ballast
- > Lamp without/with electrical socket (choice of sockets)
- > Magnet fixing (option)
- > Energy saving lamp
- > On/Off switch


The flat slimline lamp SL 025 is suitable for all types of panels and enclosures, especially where space is at a premium. The lamp can be mounted on its narrow or broad surface using screws. It is also available with a magnet which allows it to be fitted quickly in any position in a steel enclosure. Both versions are available with an integrated electrical socket enabling the use of additional appliances.

Photo: Slimline lamp with on/off switch, with integrated electric socket (Germany), Art. No. 02520.0-00



TECHNICAL DATA

Power consumption	11 W
Luminosity	900 Lm (equals 75 W light bulb)
Lamp type	energy saving lamp, 2G7 socket
Service life	10,000 h
Switch	on/off light switch
Connection	terminal 2.5 mm ² with cable clamp, torque 0.8 Nm max.
Mounting	screw fixing, M5, 300 mm centers magnet fixing (optional)
Casing	plastic according to UL94 V-0, light grey
Dimensions	345 x 91 x 40 mm
Fitting position	narrow surface/broad surface
Operating/Storage temperature	-20 to +50 °C (-4 to +122 °F) / -45 to +70 °C (-49 to +158 °F)
Operating/Storage humidity	max. 90 % RH (non-condensing)
Protection type	IP20



Art. No.	Model	Operating voltage	Socket	Nominal current	Weight (approx.)	Protection class	Approvals		
02520.0-00	without magnet	AC 230 V, 50/60 Hz	Germany/Russia (1)	16.0 A	0.4 kg	I (earthed)	VDE	-	EAC
02520.1-01	with magnet	AC 230 V, 50/60 Hz	Germany/Russia (1)	16.0 A	0.5 kg	I (earthed)	VDE	-	EAC
02521.0-00	without magnet	AC 230 V, 50/60 Hz	F/PL/CZ/SK (2)	16.0 A	0.4 kg	I (earthed)	VDE	-	EAC
02521.1-04	with magnet	AC 230 V, 50/60 Hz	F/PL/CZ/SK (2)	16.0 A	0.5 kg	I (earthed)	VDE	-	EAC
02522.0-00	without magnet	AC 230 V, 50/60 Hz	Switzerland (3)	10.0 A	0.4 kg	I (earthed)	VDE	-	EAC
02522.1-01	with magnet	AC 230 V, 50/60 Hz	Switzerland (3)	10.0 A	0.5 kg	I (earthed)	VDE	-	EAC
02523.0-00	without magnet	AC 230 V, 50/60 Hz	UK/Ireland (4)	13.0 A	0.4 kg	I (earthed)	VDE	-	EAC
02523.1-05	with magnet	AC 230 V, 50/60 Hz	UK/Ireland (4)	13.0 A	0.5 kg	I (earthed)	VDE	-	EAC
02524.0-01	without magnet	AC 120 V, 50/60 Hz	USA/Canada (5)	15.0 A	0.4 kg	I (earthed)	-	UL File No. E234324	EAC
02524.1-05	with magnet	AC 120 V, 50/60 Hz	USA/Canada (5)	15.0 A	0.5 kg	I (earthed)	-	UL File No. E234324	EAC
02527.0-00	without magnet	AC 230 V, 50/60 Hz	none	-	0.4 kg	II (double insulated)	VDE	UL File No. E234324	EAC
02527.1-14	with magnet	AC 230 V, 50/60 Hz	none	-	0.5 kg	II (double insulated)	VDE	-	EAC
02527.0-10	without magnet	AC 120 V, 50/60 Hz	none	-	0.4 kg	II (double insulated)	-	UL File No. E234324	EAC
02527.1-11	with magnet	AC 120 V, 50/60 Hz	none	-	0.5 kg	II (double insulated)	-	UL File No. E234324	EAC
02525.0-00	without magnet	DC 24 – 48 V	none	-	0.4 kg	II (double insulated)	VDE	UL File No. E234324	EAC
02525.1-01	with magnet	DC 24 – 48 V	none	-	0.5 kg	II (double insulated)	VDE	UL File No. E234324	EAC

Note: The slimline lamp SL 025 is also available with a 19" front panel.