

148-90051

Article Number: 148-90051



Description: HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 5-Port, (PC), Blue, 300/pkg

Base Data	
Local Order Number	HCPM-5
Type	HCPM-5
Color	Blue (BU) Clear (CL)
Features and benefits	<ul style="list-style-type: none"> • Double-spring technology for safe, secure and reliable connections. • Smaller footprint fits in tight spaces. • Low insertion force makes installation of solid or stranded copper wire fast and easy. • Color coded for easy identification of size. • Each port accepts multiple wire diameters for flexible applications. • Accepts 12–22 AWG solid wire and 14–22 AWG stranded wire.
Quantity Per	pack
Brand Family	HelaCon
Product Description	HelaCon Plus Mini Wire Connectors replace traditional twist-on wire connectors. They provide faster, easier and more reliable connection and distribution of cable and conductors in electrical installation applications. Mini connectors have a compact footprint and can be applied tool-free using convenient, push-in simplicity. Internal double-spring technology is approved for solid and stranded wires.
GLOBAL PART NAME (auto set)	HCPM-5-PC-BU/CL
Voltage Rating (cULus)	600 V
Voltage Rating (VDE)	450 V
Short Description	HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 5-Port, (PC), Blue, 300/pkg
Product Dimensions	
Length L (Imperial)	0.65"
Length L (Metric)	16.5mm
Max Current	24A
Max Voltage	600V
Number of Conductors	5
Width W (Imperial)	0.93"
Width W (Metric)	23.7mm

148-90051

HellermannTyton

Product Dimensions	Height H (Imperial)	0.30"
	Height H (Metric)	7.70mm
	Depth D (metric)	16.5mm
	Depth D (imperial)	0.65"
Material and Specifications		
	Material	Polycarbonate (PC)
	Material Shortcut	PC
	Flammability	UL 94 V0
	Halogenfree	Yes
	Operating Temperature	-22°F to +185°F (-30°C to +85°C)
	ROHS Compliant	Yes
	UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes	
Logistic and Packaging		
	Package Quantity (Imperial)	300
	Package Quantity (Metric)	300Pieces