

No	Murata P/N	Size (mm/inch)	TC Code	Rated Vol	Cap.
1	GJM1555C1HR10BB01	1005M/0402	C0G	50Vdc	0.1pF
2	GJM1555C1HR20BB01	1005M/0402	C0G	50Vdc	0.2pF
3	GJM1555C1HR30BB01	1005M/0402	C0G	50Vdc	0.3pF
4	GJM1555C1HR40BB01	1005M/0402	C0G	50Vdc	0.4pF
5	GJM1555C1HR50BB01	1005M/0402	C0G	50Vdc	0.5pF
6	GJM1555C1HR60BB01	1005M/0402	C0G	50Vdc	0.6pF
7	GJM1555C1HR70BB01	1005M/0402	C0G	50Vdc	0.7pF
8	GJM1555C1HR80BB01	1005M/0402	C0G	50Vdc	0.8pF
9	GJM1555C1HR90BB01	1005M/0402	C0G	50Vdc	0.9pF
10	GJM1555C1H1R0CB01	1005M/0402	C0G	50Vdc	1.0pF
11	GJM1555C1H1R1CB01	1005M/0402	C0G	50Vdc	1.1pF
12	GJM1555C1H1R2CB01	1005M/0402	C0G	50Vdc	1.2pF
13	GJM1555C1H1R3CB01	1005M/0402	C0G	50Vdc	1.3pF
14	GJM1555C1H1R5CB01	1005M/0402	C0G	50Vdc	1.5pF
15	GJM1555C1H1R6CB01	1005M/0402	C0G	50Vdc	1.6pF
16	GJM1555C1H1R8CB01	1005M/0402	C0G	50Vdc	1.8pF
17	GJM1555C1H2R0CB01	1005M/0402	C0G	50Vdc	2.0pF
18	GJM1555C1H2R2CB01	1005M/0402	C0G	50Vdc	2.2pF
19	GJM1555C1H2R4CB01	1005M/0402	C0G	50Vdc	2.4pF
20	GJM1555C1H2R7CB01	1005M/0402	C0G	50Vdc	2.7pF
21	GJM1555C1H3R0CB01	1005M/0402	C0G	50Vdc	3.0pF
22	GJM1555C1H3R3CB01	1005M/0402	C0G	50Vdc	3.3pF
23	GJM1555C1H3R6CB01	1005M/0402	C0G	50Vdc	3.6pF
24	GJM1555C1H3R9CB01	1005M/0402	C0G	50Vdc	3.9pF
25	GJM1555C1H4R0CB01	1005M/0402	C0G	50Vdc	4.0pF
26	GJM1555C1H4R3CB01	1005M/0402	C0G	50Vdc	4.3pF
27	GJM1555C1H4R7CB01	1005M/0402	C0G	50Vdc	4.7pF
28	GJM1555C1H5R0CB01	1005M/0402	C0G	50Vdc	5.0pF
29	GJM1555C1H5R1DB01	1005M/0402	C0G	50Vdc	5.1pF
30	GJM1555C1H5R6DB01	1005M/0402	C0G	50Vdc	5.6pF
31	GJM1555C1H6R0DB01	1005M/0402	C0G	50Vdc	6.0pF
32	GJM1555C1H6R2DB01	1005M/0402	C0G	50Vdc	6.2pF
33	GJM1555C1H6R8DB01	1005M/0402	C0G	50Vdc	6.8pF
34	GJM1555C1H7R0DB01	1005M/0402	C0G	50Vdc	7.0pF
35	GJM1555C1H7R5DB01	1005M/0402	C0G	50Vdc	7.5pF
36	GJM1555C1H8R0DB01	1005M/0402	C0G	50Vdc	8.0pF
37	GJM1555C1H8R2DB01	1005M/0402	C0G	50Vdc	8.2pF
38	GJM1555C1H9R0DB01	1005M/0402	C0G	50Vdc	9.0pF
39	GJM1555C1H9R1DB01	1005M/0402	C0G	50Vdc	9.1pF
40	GJM1555C1H100JB01	1005M/0402	C0G	50Vdc	10pF
41	GJM1555C1H120JB01	1005M/0402	C0G	50Vdc	12pF
42	GJM1555C1H150JB01	1005M/0402	C0G	50Vdc	15pF
43	GJM1555C1H180JB01	1005M/0402	C0G	50Vdc	18pF
44	GJM1555C1H200JB01	1005M/0402	C0G	50Vdc	20pF
45	GJM1555C1H220JB01	1005M/0402	C0G	50Vdc	22pF
46	GJM1555C1H270JB01	1005M/0402	C0G	50Vdc	27pF

47	GJM1555C1H330JB01	1005M/0402	C0G	50Vdc	33pF
48	GJM1555C1H390JB01	1005M/0402	C0G	50Vdc	39pF
49	GJM1555C1H470JB01	1005M/0402	C0G	50Vdc	47pF

±5%	0.55max	20
±5%	0.55max	20
±5%	0.55max	20