



R4300 Printer Ribbon

Part Number:

R4311

Ribbon Size:

1 in W x 984 ft L

For Use with Printer:

BBP®72 Label Printer, BBP®81 Label Printer, BRADY MVP Plus Series, BRADY X Plus II Series Label Machine, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer, TAGUS™ Thermal Transfer Printer, WRAPTOR™ Wire Marking System



OVERVIEW

This ink-side-out ribbon features an open 1 in. core for compatibility with a wide variety of thermal transfer printers.

- One-color ribbon for printing a single color onto a label
- R4300 Series Ribbons offers strong environmental resistance against smearing and chemicals when printed on the appropriate Brady® label material
- Recommended for printing on paper and films that have a matte or rough surface, such as B-427 Self-Laminating Vinyl and B-499 Nylon Cloth from Brady®
- Combine Brady label materials with their recommended ribbon series for superior legend performance

• SPECIFICATIONS

Core Diameter	1 in
UOM	Roll of 984 Feet
Product Number	10615
UPC	662820106159
Ribbon Color Options	Single Color Ribbon
Ribbon Formulation Type	Resin/Wax
Ribbon Ink Wind Direction	Side Out
Ribbon Roll Type	Open Core Ribbon
Ribbon Series	R4300
Ribbon Size	1 in W x 984 ft L
Ribbon Size(m)	25.4 mm W x 299.92 m L
Ribbon Width	1 in
Roll Length	984 ft
Color	Black
For Use with Printer	BBP®72 Label Printer, BBP®81 Label Printer, BRADY MVP Plus Series, BRADY X Plus II Series Label Machine, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer, TAGUS™ Thermal Transfer Printer, WRAPTOR™ Wire Marking System
Label/Media Format	Open Core Ribbon
Resistance Properties	Chemical-Resistant, Smear-Resistant