

## PA-2400RC - PA Desk Microphone



**PA zone paging desktop microphone**, for connection to PA-2410Z and PA-2420Z.

- Selection buttons for speaker zones 1-20
- Start/stopp function for 6 selectable announcements which are stored in the digital module PA-1120DMT, available at option
- LED indication for various functions
- Automatic chime via microphone announcement button
- Adjustable microphone sensitivity
- 24 V power supply via PA-2410Z, PA-2420Z
- RJ45 jacks for connection to additional PA-2400RC with slave/priority switch
- Up to 3 x PA-2400RC can be connected to PA-2410Z or PA-2420Z
- Supplied with 3 m connection cable (Cat. 5e)

## Technical Data

Type	: PA desktop microphone
Version	: -
Transmission method	: cable
Polar pattern	: -
System	: -
Carrier frequency range	: -
Transmitting power	: -
Power supply	: via PA-2410Z, PA-2420Z
Operating time	: -
Audio frequency range	: -
Nominal impedance	: -
Sensitivity	: -
S/N ratio	: -
Maximum sound pressure	: -
Power supply	: -
Gooseneck length	: -
Material (housing/cabinet)	: -
Admiss. ambient temp.	: 0-40 °C
Dimensions	: 275 x 51 x 156 mm (console housing)
Weight	: 1.4 kg
Cable	: -
Connection	: RJ45 (input/link)